

Datasheet Expansion alloys

# Osprey<sup>®</sup> Alloy 36

Osprey<sup>®</sup> Alloy 36 is an expansion alloy with a low coefficient of thermal expansion. It is typically used in aerospace components, radio-electronic, optical and laser systems.

UNS K93600	
ASTM, AISI F1684	
EN Number 1.3912	Osprey® Metal Powder
W. Nr. 1.3912	
Powder designed for	

Additive Manufacturing (AM)

### **Product description**

Osprey<sup>®</sup> Alloy 36 is an expansion alloy with a low coefficient of thermal expansion. It is typically used in aerospace components, radio-electronic, optical and laser systems. Osprey<sup>®</sup> Alloy 36 is an alloy of the same type as Invar<sup>®</sup> 36<sup>\*</sup>.

This metal powder is manufactured by Inert Gas Atomization (IGA), producing a powder with a spherical morphology which provides good flow characteristics and high packing density. In addition, the powder has a low oxygen content and low impurity levels, resulting in a metallurgically clean product with enhanced mechanical performance.



\*Invar® is a trademark owned by Aperam Alloys Imphy.



# Chemical composition (nominal), %

Last updated: Jul 18, 2023 9:10 AM CET

Fe	Bal.
Ni	35-37
С	0.02
Mn	0.5
Si	0.25

#### Powder characteristics and morphology Powder for Additive Manufacturing


Osprey<sup>®</sup> metal powder for Additive Manufacturing is characterized by a spherical morphology and high packing density, which confer good flow properties. For powder bed processes these are essential when applying fresh powder layers to the bed to ensure uniform and consistent part build.

For blown powder processes, such as Direct Energy Deposition (DED), good flow ensures uniform build rates. Tight control of the particle size distribution also helps ensure good flowability. Low oxygen powders result in clean microstructures and low inclusion levels in the finished parts.

### Particle size distribution

#### Powder for Additive Manufacturing

Osprey<sup>®</sup> metal powder for Additive Manufacturing is available in a wide range of particle size distributions that are tailored to the individual Additive Manufacturing systems. They can also be tailored to the particular requirements of the end application, both in terms of mechanical performance and surface finish.





Process technology	Size (µm)
Binder jetting	≤ 16, ≤ 22, ≤ 32, ≤ 38, ≤ 45
Laser - Powder Bed Fusion (L-PBF)	15 to 53 and 10 to 45
Electron beam - Powder Bed Fusion (E-PBF)	45 to 106
Direct Energy Deposition (DED)	53 to 150

Tailor-made particle size distributions are available on request.Contact us to discuss your specific requirements.

# Testing

All Osprey<sup>®</sup> metal powders are supplied with a certificate of analysis containing information on the chemical composition and particle size distribution. Information on other powder characteristics is available upon request.

# Packaging

A wide range of packaging options is available, from 5kgs plastic bottles to 250kg metal drums.

5 kg (11 lbs) Plastic bottles 6 kg (13 lbs) Plastic bottles 10 kg (22 lbs) Plastic bottles 20 kg (44 lbs) Metal cans 100 kg (220 lbs) Steel drums 150 kg (330 lbs) Steel drums 250 kg (551 lbs) Steel drums All packaging materials are suitable for air, sea and road freight.

Contact us for more information and to discuss your packaging requirements.

Disclaimer: Data and recommendations are provided for information and guidance only, and the performance or suitability of the material for specific applications are not warranted or guaranteed. Continuous development may necessitate changes in technical data without notice. This datasheet is only valid for Sandvik materials. Datasheet updated: Sep 8, 2023 2:10 PM CET (supersedes all previous editions)